Data Sheet: LDS 1386

Date: 26-03-2013

Product: Noga Slot Cleaner: NG 3210

Page 1 of 2



Used to relieve corners in narrow slots from 3.5mm wide Includes: NG-3 Handle, L Holder and L5 Blade

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
NG 3210	Slot Cleaner	86	30	30	180

Instructions
Do not use heavy pressure when deburring as this will cause the blade to dig into the material and give an uneven finish Use light and even pressure which will allow the blade and handle to work together to remove the burr and leave a smooth finish on the component Blades should be handled carefully as they are sharp and can cut Blades can break causing flying objects Sharp edges and flying objects can cause injury Users and bystanders should wear protective safety glasses Do not pry or bend blades Keep blades and sharp tools away from children Do not regrind blades as this will weaken the blade and cause breakage and possible injury All Noga products meet the strict requirements of ISO 9001 and ISO 14001

NG-3 Handle

	NG-3 Handle accepts all Blade Holders Ergonomic soft grip, acetyl and rubber construction Removable end cap for blade storage 125mm long x 28mm maximum diameter
--	---

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
NG-3 Handle	NG3000	45	32	32	153

L Holder

	Holds L3, L4, L5, L6 & L7 Blades Used in NG-3 Handle Telescopes from 30 to 115mm in Handle Blade attached to Holder by cap screw
--	---

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
EL 07013	L Holder	40	23	23	153

Copyright: Linear Tools 2013

Data Sheet: LDS 1386

Product: Noga Slot Cleaner: NG 3210

Page 2 of 2

L5 Blade

		Replacement Blade for Slot Cleaner Tool (NG 3210) Works best on slots from 3.5mm Included Angle: 65° Material: HSS Hardness: 62-64 HRC Fits to L Holder (ELO7013)
--	--	--

Packed Weight and Dimensions

Code	Description	Pack	Weight g	W mm	H mm	Lmm
		Quantity				
BL5001	Replacement Blade for Slot Cleaner	10	20	36	21	70